



































# SPONGE SECTIONS

COMPOUND – E.P.D.M. • STANDARD COIL LENGTH 20 METRES • MAX OPERATING TEMPERATURE 120°C

\*PICTURES ARE INDICATIVE ONLY

						
<b>S1</b> PAS001 4.8x3.2mm	<b>S2</b> PAS002 9.5x6.4mm	<b>S3</b> PAS003 9.5x9.5mm	<b>S4</b> PAS004 9.5x12.7mm	<b>S5</b> PAS005 12.7x19.1mm	<b>S6</b> PAS006 12.7x9.5mm	<b>S7</b> PAS007 25x16mm
						
<b>S8</b> PAS008 24x12mm	<b>S9</b> PAS009 19x19mm	<b>S10</b> PAS010 4.8x15.9mm	<b>S11</b> PAS011 12x12mm	<b>S12</b> PAS012 22x12mm	<b>S13</b> PAS013 18x10mm	<b>S14</b> PAS014 16x9.5mm
						
<b>S15</b> PAS015 12x12mm	<b>S16</b> PAS016 10x10mm	<b>S17</b> PAS017 18x7mm	<b>S18</b> PAS018 ø9mm	<b>S19</b> PAS019 ø12mm	<b>S21</b> PAS021 ø16mm	<b>S22</b> PAS022 ø19mm
						
<b>S23</b> PAS023 10x12mm	<b>S24</b> PAS024 17x14mm	<b>S25</b> PAS025 15x14.5mm	<b>S26</b> PAS026 38.1x12.7mm	<b>S27</b> PAS027 12.7x12.2	<b>S28</b> PAS028 7.9x4.8mm	
						
<b>S29</b> PAS029 12.7x3.2mm	<b>S30</b> PAS030 25.4x6.4mm	<b>S31</b> PAS031 25.4x12.7mm	<b>S32</b> PAS032 63.5x12.7mm	<b>S33</b> PAS033 6.4x3.2mm	<b>S34</b> PAS034 9.5x14.3x6.4mm	<b>S124</b> PAS124 19x14mm

## Rectangular Hatch Seal Sections

<b>S164</b> PAS164 40x30mm	<b>S32</b> PAS032 63.5x12.7mm	<b>S102</b> PAS102 40x20mm	<b>S200</b> PAS200 35x70mm
----------------------------------	-------------------------------------	----------------------------------	----------------------------------

## RECOMMENDED ADHESIVE

Skellerup **Superspan EPDM** is the only adhesive for EPDM Sponge.  
Available in 50ml tube(SEA005),500ml (SEA050).

Specification may be subject to change without notice.